



Pushing Performance
Since 1945

har-port USB charger 5V/1,5A black



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1980
Specification	har-port USB charger 5V/1,5A black
HARTING eCatalogue	https://b2b.harting.com/09454521980

Identification

Category	Connectors
Series	har-port
Element	Charging set
Specification	USB 3.0

Version

Connection type	Type A jack
Fixing	Screwable in cover plates

Technical characteristics

Output current	1.5 A
Input voltage	12 ... 24 V DC
Output voltage	5 V DC $\pm 0,25$
Operating temperature	-40 ... +55 °C
Storage temperature	-40 ... +80 °C
Mating cycles	$\geq 1,500$
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Black
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	30 g
Country of origin	Germany
European customs tariff number	85043121
GTIN	5713140223042
ETIM	EC002599
eCl@ss	27060304 Appliance cord (data cable)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09454521980](#)