



Pushing Performance  
Since 1945

# Han3A RJ45 PFT adapter w/o clip



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 515 0022
Specification	Han3A RJ45 PFT adapter w/o clip
HARTING eCatalogue	<a href="https://b2b.harting.com/09455150022">https://b2b.harting.com/09455150022</a>

## Identification

Category	Connectors
Series	RJ45
Element	Adapter
Specification	for fixing of RJ45 jacks

## Version

Size	3 A
Shielding	Unshielded

## Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

## Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance  
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Specifications	EN 45545-2
Approvals	DNV GL

Commercial data

Packaging size	100
Net weight	2.14 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140060937
ETIM	EC002310
eCl@ss	27440210 Fixing element for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09455150022](#)