

Han3A RJ45 Hybrid power jack SMD T&R



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 525 0041
Specification	Han3A RJ45 Hybrid power jack SMD T&R
HARTING eCatalogue	https://b2b.harting.com/09455250041

Identification

Category	Connectors
Series	RJ45 Hybrid
Element	Power module
Specification	for direct device integration

Version

Termination method	Reflow soldering termination (SMT)
Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	0
Pack contents	100 pieces on reel

Technical characteristics

Conductor cross-section	1.5 mm ²
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	100
Net weight	6 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140060999
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09455250041](#)