

HPP V4 Hybrid PCB jack straight, 4+3p



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 545 1300
Specification	HPP V4 Hybrid PCB jack straight, 4+3p
HARTING eCatalogue	https://b2b.harting.com/09455451300

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	Hybrid
Element	Inserts
Specification	Straight

Version

Termination method	Solder termination
Shielding	Unshielded
Number of contacts	7
Number of data contacts	4
Number of power contacts	3

Technical characteristics

Rated current	5 A
Rated voltage	48 V
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	2.22 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140061224
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09455451300](#)