



Pushing Performance
Since 1945

RJI RJ45 8-port jack Cat.5 THT angled




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 551 1128
Specification	RJI RJ45 8-port jack Cat.5 THT angled
HARTING eCatalogue	https://b2b.harting.com/09455511128

Identification

Category	Connectors
Series	HARTING RJ Industrial®
Element	Female
Specification	RJ45
	Angled
	8 ports

Version

Termination method	Wave soldering termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8

Technical characteristics

Rated current	1.5 A
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
Limiting temperature	-40 ... +85 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20

Material properties

Material flammability class acc. to UL 94	V-0
---	-----



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

UL / CSA	UL 1977 DUXR2.E254191
	CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E254191
Approvals	DNV GL

Commercial data

Packaging size	30
Net weight	38.18 g
Country of origin	Taiwan
European customs tariff number	85366990
GTIN	5713140061613
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09455511128](#)