




Pushing Performance
Since 1945

HARTING SEA CABLE S/FTP CAT 7 100m



Part number	09 45 600 0525
Specification	HARTING SEA CABLE S/FTP CAT 7 100m
HARTING eCatalogue	https://b2b.harting.com/09456000525

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)
Features	Flame retardant, halogen free and RoHS compliant Oil and UV resistant

Version

Cable length	100 m
Number of cores	8
Core structure	4x 2x AWG 26/7

Technical characteristics

Transmission characteristics	Cat. 7 Class II up to 2000 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +80 °C
Cable diameter	7.1 mm
Minimum bending radius	10x Cable diameter (repeated bending)
	5x Cable diameter (singular bending)
Test voltage U _{r.m.s.}	1 kV Wire / wire / shielding
Coupling attenuation @ 20 °C / 100 MHz	10 mΩ/m



Pushing Performance
Since 1945

Technical characteristics

Conductor resistance @ 20 °C	≤290 Ω/km
Insulation resistance @ 20 °C	≥500 MΩ x km
Signal run time @ 20 °C	≤5.3 ns/m
Impedance @ 100 MHz	100 Ω ±5 %

Material properties

Material (cable)	FRNC (LSZH)
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 60754-2 Non corrosive
	IEC 61034 Smoke density
	IEC 60811-404 Oil resistance
	IEC 60332-1-2 Flame retardancy
	IEC 60332-3-22 Flame retardancy
	Directive 2011/65/EU
	Directive 2015/863/EU
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	5,981 g
Country of origin	Germany
European customs tariff number	85444995
GTIN	5713140273672
ETIM	EC003249
eCl@ss	27061801 Data and communication cable (copper)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09456000525](#) [9456000525](#)