

RJ45 M12 D-cod EtherRail Cable Assy, 3,0m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 022 2011 030
Specification	RJ45 M12 D-cod EtherRail Cable Assy, 3,0m
HARTING eCatalogue	https://b2b.harting.com/09480222011030

Identification

Category	System cabling
Series	Circular connectors M12 RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Straight Overmoulded
Connector 2	RJ45 Overmoulded
Type of cable	Copper cable (round)

Version

Cable length	3 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +85 °C unmoved -25 ... +70 °C moved
Cable diameter	6.6 mm ± 0.2 mm



Pushing Performance
Since 1945

Technical characteristics

Minimum bending radius	6x Cable diameter (repeated bending)
	5x Cable diameter (singular bending)
Impedance	100 Ω \pm 5 %

Material properties

Material (cable)	Elastomer
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	EN 45545-2
----------------	------------

Commercial data

Packaging size	1
Net weight	235.6 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140266094
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09480222011030](#)