



Pushing Performance
Since 1945

MPP-ACC-DUST CAP DEVICE LANYARD IP65/67



Image is for illustration purposes only. Please refer to product description.

Part number	09 51 800 0003
Specification	MPP-ACC-DUST CAP DEVICE LANYARD IP65/67
HARTING eCatalogue	https://b2b.harting.com/09518000003

Identification

Category	Accessories
Series	HARTING Mini PushPull
Type of accessory	Protection cover
Description of the accessory	for device side

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Limiting temperature	-40 ... +70 °C
Storage temperature	-60 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67

Material properties

Material (seal)	NBR
Colour (seal)	Black
Material (accessories)	Polybutylene terephthalate (PBT)
Colour (accessories)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140235595
ETIM	EC002943
eCl@ss	27440292 Connector component (accessories)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09518000003](#)