



Pushing Performance
Since 1945

Set Han3A M plug 2x LC duplex SM GOF



Image is for illustration purposes only. Please refer to product description.

Part number	09 57 407 0002 000
Specification	Set Han3A M plug 2x LC duplex SM GOF
HARTING eCatalogue	https://b2b.harting.com/09574070002000

Identification

Category	Connectors
Series	LC duplex
Element	Cable connector
Type of contact	LC contact
Description of the contact	Singlemode
Type of hood/housing	Hood
Description of hood/housing	Straight

Version

Size	3 A
Number of contacts	4

Technical characteristics

Limiting temperature	-40 ... +70 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	Black
RoHS	compliant with exemption



Pushing Performance
Since 1945

Material properties

RoHS exemptions	6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0,4 % by weight 6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel
	Naphthalene

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	157.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140224131
ETIM	EC002636
eCl@ss	27440113 Rectangular connectors (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09574070002000](#)