

Set Han3A receptacle DC LC duplex SM GOF



Image is for illustration purposes only. Please refer to product description.

Part number	09 57 568 0511 000
Specification	Set Han3A receptacle DC LC duplex SM GOF
HARTING eCatalogue	https://b2b.harting.com/09575680511000

Identification

Category	Connectors
Series	LC duplex Hybrid
Element	Panel feed through
Type of contact	LC contact
Description of the contact	Singlemode
Type of hood/housing	Hood

Version

Size	3 A
Number of contacts	2
Contact configuration	V+, GND, V-
further contacts	+ 3x 300 V DC

Technical characteristics

Limiting temperature	-40 ... +70 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	Black
RoHS	compliant with exemption



Pushing Performance
Since 1945

Material properties

RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	89.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140072824
ETIM	EC002636
eCl@ss	27440113 Rectangular connectors (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09575680511000](#)