

UIC 558 22PIN SOCKET KIT-FC-AU



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 022 1013
Specification	UIC 558 22PIN SOCKET KIT-FC-AU
HARTING eCatalogue	https://b2b.harting.com/09580221013

Identification

Category	Connector sets
Series	HARTING UIC
Identification	558
Element	Connector sets

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	22
PE contact	Yes
Details	Crimp contacts enclosed separatly

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	110 V
Insulation resistance	>10 ⁷ Ω
Contact resistance	≤4 mΩ
Stripping length	5 mm
Tightening torque	5 Nm Fixing screws M6
Limiting temperature	-50 ... +125 °C
Mating cycles	≥10,000



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition IP67 unmated condition & cover closed
--	---

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7035 (light grey) RAL 5010 (gentian blue)
Material (seal)	Silicone
Material (locking)	Stainless steel
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

Commercial data

Packaging size	1
Net weight	592 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140190375
ETIM	EC002635
eCl@ss	27440115 Circular connector (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09580221013](#)