

## Han 3 EMC Base Surface 1 Lever 1 Entry P



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 003 1250
Specification	Han 3 EMC Base Surface 1 Lever 1 Entry P
HARTING eCatalogue	<a href="https://b2b.harting.com/09620031250">https://b2b.harting.com/09620031250</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® EMC
Type of hood/housing	Surface mounted housing

### Version

Size	3 A
Version	Top entry
Cable entry	1x Pg 11
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements
Pack contents	Please order seal screw separately.

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44
	IP65 With seal screw
	IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted



**Pushing Performance**  
Since 1945

## Material properties

Material (seal)	PTFE
Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

## Commercial data

Packaging size	10
Net weight	82 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140073074
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09620031250](#)