



Pushing Performance  
Since 1945

# Han EMC 64 Hood Top Entry PG 21



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 064 0440
Specification	Han EMC 64 Hood Top Entry PG 21
HARTING eCatalogue	<a href="https://b2b.harting.com/09620640440">https://b2b.harting.com/09620640440</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han® EMC
Type of hood/housing	Hood

## Version

Size	24 B
Version	Top entry
Cable entry	1x Pg 21
Locking type	Screw locking
Field of application	Hoods/Housings for higher EMC requirements

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant



**Pushing Performance**  
Since 1945

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

## Commercial data

Packaging size	1
Net weight	397.2 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140073678
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09620640440](#)