



Pushing Performance  
Since 1945

# D SUB MIXED MA PNEUMATIC CONTACT\_3 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 69 287 0062
Specification	D SUB MIXED MA PNEUMATIC CONTACT_3 mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09692870062">https://b2b.harting.com/09692870062</a>

## Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Pneumatic contact

## Version

Gender	Male
Manufacturing process	Turned contacts

## Technical characteristics

Limiting temperature	-10 ... +60 °C
Tube inner diameter	3 mm

## Material properties

Material (contacts)	German silver
Material (seal)	Viton
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance  
Since 1945

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	20
Net weight	1.9 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140099609
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09692870062](#)