



Pushing Performance
Since 1945

Han3A RJ45 Hybrid Cat5 plug 4+4p



Image is for illustration purposes only. Please refer to product description.

Part number	10 12 005 2001
Specification	Han3A RJ45 Hybrid Cat5 plug 4+4p
HARTING eCatalogue	https://b2b.harting.com/10120052001

Identification

Category	Connectors
Series	RJ45 Hybrid
Element	Cable connector
Type of hood/housing	Hood
Description of hood/housing	Straight

Version

Termination method	IDC termination
Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Number of data contacts	4
Number of power contacts	4

Technical characteristics

Conductor cross-section	0.22 ... 0.32 mm² Stranded (Data)
	0.26 ... 0.32 mm² Solid (Data)
	1.5 mm² Power
Conductor cross-section	AWG 24 ... AWG 22 Stranded (Data)
	AWG 23 ... AWG 22 Solid (Data)
	AWG 16 Power
Rated voltage (Data)	50 V AC
	60 V DC
Rated voltage (power)	48 V DC
Rated current (data)	1.76 A



Pushing Performance
Since 1945

Technical characteristics

Rated current (power)	16 A
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Cable diameter	10 ... 11 mm

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	Grey
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	10
Net weight	40 g
Country of origin	Romania



Pushing Performance
Since 1945

Commercial data

European customs tariff number	85366990
GTIN	5713140108448
ETIM	EC002636
eCl@ss	27440113 Rectangular connectors (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[10120052001](#)