

Han HPR SP3 185mm² shielded w/ CG



Image is for illustration purposes only. Please refer to product description.

Part number	10 40 331 1115
Specification	Han HPR SP3 185mm² shielded w/ CG
HARTING eCatalogue	https://b2b.harting.com/10403311115

Identification

Category	Connector sets
Series of hoods/housings	Han® HPR TrainPowerLine
Element	Connector sets
Specification	With cable gland

Version

Shielding	Shielded
Number of contacts	1
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Conductor cross-section	185 mm²
Rated current	800 A
Rated voltage	5,100 V DC 3,000 V AC

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
-------------------------	---



Pushing Performance
Since 1945

Specifications and approvals

Specifications	EN 50124-1
	EN 50467
	IEC 61373 Category 1 Class B
	UIC 550
	UIC 552

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140190078
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[10403311115](#)