

## Han-Yellock F-c 1mm<sup>2</sup> (Ag)



Image is for illustration purposes only. Please refer to product description.

Part number	11 05 000 6204
Specification	Han-Yellock F-c 1mm <sup>2</sup> (Ag)
HARTING eCatalogue	<a href="https://b2b.harting.com/11050006204">https://b2b.harting.com/11050006204</a>

### Identification

Category	Contacts
Series	Han-Yellock®
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	1 mm <sup>2</sup>
Conductor cross-section	AWG 18
Rated current	≤20 A
Contact resistance	≤2 mΩ
Stripping length	6.5 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	100
Net weight	0.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140109513
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[11050006204](#)