

## Han Yellock 30HSM 1xM20 with bulkhead h.



Image is for illustration purposes only. Please refer to product description.

Part number	11 12 300 1210
Specification	Han Yellock 30HSM 1xM20 with bulkhead h.
HARTING eCatalogue	<a href="https://b2b.harting.com/11123001210">https://b2b.harting.com/11123001210</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Surface mounted housing
Description of hood/housing	incl. bulkhead mounted housings

### Version

Size	Han-Yellock® 30
Version	Side entry
Cable entry	1x M20
Locking type	Screw locking
Field of application	Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7021 (black grey)



**Pushing Performance**  
Since 1945

## Material properties

Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

## Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
Approvals	CE
	DNV GL

## Commercial data

Packaging size	1
Net weight	535 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140109940
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[11123001210](#)