

## Han-Yellock 60 HSM 2xM32



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 11 12 600 1206  |
| Specification      | Han-Yellock 60 HSM 2xM32  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/11126001206">https://b2b.harting.com/11126001206</a> |

### Identification

|                          |                         |
|--------------------------|-------------------------|
| Category                 | Hoods/Housings          |
| Series of hoods/housings | Han-Yellock®            |
| Type of hood/housing     | Surface mounted housing |

### Version

|                      |  |
|----------------------|--|
| Size                 | Han-Yellock® 60                            |
| Version              | Side entry                                 |
| Cable entry          | 2x M32                                     |
| Locking type         | Screw locking                              |
| Field of application | Hoods/housings for industrial applications |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Un-/locking temperature                | -10 ... +85 °C                                 |
| Degree of protection acc. to IEC 60529 | IP65<br>IP67                                   |

### Material properties

|                         |                       |
|-------------------------|-----------------------|
| Material (hood/housing) | Zinc die-cast         |
| Surface (hood/housing)  | Powder-coated         |
| Colour (hood/housing)   | RAL 7021 (black grey) |
| Material (seal)         | NBR                   |



**Pushing Performance**  
Since 1945

## Material properties

|   |               |
|---|---------------|
| Material flammability class acc. to UL 94 | V-0           |
| RoHS                                      | compliant     |
| ELV status                                | compliant     |
| China RoHS                                | e             |
| REACH Annex XVII substances               | Not contained |
| REACH ANNEX XIV substances                | Not contained |
| REACH SVHC substances                     | Not contained |
| California Proposition 65 substances      | Yes           |
| California Proposition 65 substances      | Nickel        |

## Specifications and approvals

|                |             |
|----------------|-------------|
| Specifications | IEC 60664-1 |
|                | IEC 61984   |
| Approvals      | CE          |
|                | DNV GL      |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 580 g                                    |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140110250                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[11126001206](#)