

Han-Yellock 60 M bulkhead housing, molly



Image is for illustration purposes only. Please refer to product description.

Part number	11 13 600 0302
Specification	Han-Yellock 60 M bulkhead housing, molly
HARTING eCatalogue	https://b2b.harting.com/11136000302

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Bulkhead mounted housing

Version

Size	Han-Yellock® 60
Field of application	Hoods/housings for outdoor applications
Pack contents	incl. 4 panel fastener

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Passivated
Colour (hood/housing)	Metallic
Material (seal)	NBR
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
Approvals	CE
	DNV GL

Commercial data

Packaging size	1
Net weight	139.76 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140110571
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[11136000302](#)