

Spec. Cable Gland M25 Cable-Ø13-21 SBC



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5019
Specification	Spec. Cable Gland M25 Cable-Ø13-21 SBC
HARTING eCatalogue	https://b2b.harting.com/19000005019

Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Tightening torque	10 Nm
Wrench size	32
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65 / IP68
Size	M25
Clamping range	13 ... 21 mm
Width across corners	33.4 mm

Material properties

Material (seal)	EPDM
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	100 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140123588
ETIM	EC000441
eCl@ss	27140803 Cable gland EMC (electrical installation)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19000005019](#)