

## Han CGM-M M40x1,5 D.19-28mm E.47



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5078
Specification	Han CGM-M M40x1,5 D.19-28mm E.47
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005078">https://b2b.harting.com/19000005078</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-M
Type of accessory	Cable gland

### Technical characteristics

Wrench size	43 40
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M40
Clamping range	19 ... 28 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated

### Specifications and approvals

Approvals	DNV GL
-----------	--------

### Commercial data

Packaging size	1
----------------	---



**Pushing Performance**  
Since 1945

## Commercial data

Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140193062
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19000005078](#)