

CABLE CLAMP M20, 6-12m, THERMOPLASTIC BL



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5132
Specification	CABLE CLAMP M20, 6-12m, THERMOPLASTIC BL
HARTING eCatalogue	https://b2b.harting.com/19000005132

Identification

Category	Accessories
Type of accessory	Cable gland

Technical characteristics

Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68
Size	M20
Clamping range	6 ... 12 mm

Material properties

Material (cable glands)	Thermoplastic
Colour (cable gland)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	10
Net weight	10.92 g



Pushing Performance
Since 1945

Commercial data

Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140123861
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19000005132](#)