



Pushing Performance  
Since 1945

# Han CGM-P M32x1,5 D.18-25mm black



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5187
Specification	Han CGM-P M32x1,5 D.18-25mm black
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005187">https://b2b.harting.com/19000005187</a>

## Identification

Category	Accessories
Series of hoods/housings	Han® CGM-P
Type of accessory	Cable gland

## Technical characteristics

Tightening torque	≤6.5 Nm (depending on the cable and the seal insert used)
Wrench size	42
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M32
Clamping range	18 ... 25 mm
Width across corners	42 mm

## Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	RAL 9005 (jet black)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

UL / CSA	UL 514B QCRV.E479780 CSA-C22.2 No. 18.3 QCRV7.E479780
Approvals	DNV GL

## Commercial data

Packaging size	10
Net weight	30 g
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140192928
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19000005187](#)