

Han Q 8/0 - GS - Metal



Image is for illustration purposes only. Please refer to product description.

Part number	19 12 008 0502
Specification	Han Q 8/0 - GS - Metal
HARTING eCatalogue	https://b2b.harting.com/19120080502

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Hood
Description of hood/housing	for Han-Compact® half cable gland for Han® Q 8/0 Crimp (max. 400 V), Han® Q17/0 and Han® Q Data RJ45

Version

Size	Han-Compact®
Version	Side entry
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 ECBT8.E235076 CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	159 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140124158
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19120080502](#)