



Pushing Performance
Since 1945

Han CGM-PVDF M25x1,5 8,0-5,0



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 15 503 5290 |
| Specification | Han CGM-PVDF M25x1,5 8,0-5,0 |
| HARTING eCatalogue | https://b2b.harting.com/19155035290 |

Identification

| | |
|--------------------------|-------------|
| Category | Accessories |
| Series of hoods/housings | Han® F+B |
| Type of accessory | Cable gland |

Technical characteristics

| | |
|--|-----------------|
| Wrench size | 27 29 |
| Limiting temperature | -40 ... +100 °C |
| Degree of protection acc. to IEC 60529 | IP68 |
| Size | M25 |
| Clamping range | 5 ... 8 mm |

Material properties

| | |
|-----------------------------|----------------|
| Material (cable glands) | Polyamide (PA) |
| Colour (cable gland) | Black |
| Material (seal) | TPE |
| Colour (seal) | Blue |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---------------|
| California Proposition 65 substances | Not contained |
|--------------------------------------|---------------|

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 50 |
| Net weight | 0.023 kg |
| Country of origin | Germany |
| European customs tariff number | 39174000 |
| GTIN | 5713140192782 |
| ETIM | EC000441 |
| eCl@ss | 27140801 Screwed cable gland (electrical) |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19155035290](#)