

Han CGM-P F+B M25X1,5 D. 11-13 nature



Image is for illustration purposes only. Please refer to product description.

Part number	19 15 523 5196
Specification	Han CGM-P F+B M25X1,5 D. 11-13 nature
HARTING eCatalogue	https://b2b.harting.com/19155235196

Identification

Category	Accessories
Series of hoods/housings	Han® F+B
Type of accessory	Cable gland

Version

Pack contents	With spacing washer
---------------	---------------------

Technical characteristics

Wrench size	32
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP67 / IP69
Size	M25
Clamping range	11 ... 13 mm

Material properties

Roughness of the surface	≤0.8 µm
Material (cable glands)	Polyamide (PA)
Colour (cable gland)	White
Colour (seal)	Blue
Material (accessories)	VA 1.4305



Pushing Performance
Since 1945

Specifications and approvals

Approvals	Ecolab Topactive 200
	Ecolab Topactive 500
	Ecolab Topax 66
	Ecolab Topactive OKTO
	Ecolab Topax 990
	FDA 21 CFR 177.1500
	FDA 21 CFR 176.170 (c)
	FDA 21 CFR 177.1390
	FDA 21 CFR 177.1395
	FDA 21 CFR 177.2600

Commercial data

Packaging size	1
Net weight	31.5 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140192799
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19155235196](#)