



Pushing Performance  
Since 1945

# 3A TE Hood, 9-17 cord grip, glued seal



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 003 0413
Specification	3A TE Hood, 9-17 cord grip, glued seal
HARTING eCatalogue	<a href="https://b2b.harting.com/19200030413">https://b2b.harting.com/19200030413</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han A <sup>®</sup>
Type of hood/housing	Hood
Description of hood/housing	for Han-Brid <sup>®</sup> With glued seal With integrated cable gland

## Version

Size	3 A
Version	Top entry
Cable entry	1x Integrated
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4 4X 12



**Pushing Performance**  
Since 1945

## Technical characteristics

Cable diameter	9 ... 17 mm
----------------	-------------

## Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

## Commercial data

Packaging size	10
Net weight	18.33 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140124387
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19200030413](#)