

Han 3A Hood Top Entry M25 Low Constr.



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 20 003 1421 |
| Specification | Han 3A Hood Top Entry M25 Low Constr. |
| HARTING eCatalogue | https://b2b.harting.com/19200031421 |

Identification

| | |
|-----------------------------|-----------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han A [®] |
| Type of hood/housing | Hood |
| Description of hood/housing | With integrated cable gland |

Version

| | |
|----------------------|---|
| Size | 3 A |
| Version | Top entry |
| Cable entry | 1x Integrated |
| Locking type | Single locking lever |
| Field of application | Standard Hoods/housings for industrial applications |
| Pack contents | Please order seal screw separately. |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP44 IP65 With seal screw IP67 With seal screw |
| Type rating acc. to UL 50 / UL 50E | 12 |
| Cable diameter | 6 ... 12 mm |

Material properties

| | |
|-------------------------|---------------|
| Material (hood/housing) | Zinc die-cast |
|-------------------------|---------------|



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|--|
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7037 (dust grey) |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| ECHA SCIP number | 564b7d75-7bf6-4cfb-acb1-2168eb61b675 |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R1 (HL 1-3) R7 (HL 1-3) |

Specifications and approvals

| | |
|-----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 73 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140124547 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19200031421](#)