



Pushing Performance  
Since 1945

# Han B Hood Top Entry HC M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 016 0428
Specification	Han B Hood Top Entry HC M40
HARTING eCatalogue	<a href="https://b2b.harting.com/19300160428">https://b2b.harting.com/19300160428</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han® B
Type of hood/housing	Hood
Type	High construction

## Version

Size	16 B
Version	Top entry
Cable entry	1x M40
Locking type	Double locking lever
Field of application	Standard hoods/housings for industrial connectors

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
	IP66
	IP67
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

Material (hood/housing)	Aluminium die-cast
-------------------------	--------------------



**Pushing Performance**  
Since 1945

## Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	185 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140126015
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19300160428](#)