



Pushing Performance  
Since 1945

# Han B Hood Top Entry HC 4 Pegs M25 black



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 30 716 0426  |
| Specification      | Han B Hood Top Entry HC 4 Pegs M25 black  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19307160426">https://b2b.harting.com/19307160426</a> |

## Identification

|                             |                   |
|-----------------------------|-------------------|
| Category                    | Hoods/Housings    |
| Series of hoods/housings    | Han® B            |
| Type of hood/housing        | Hood              |
| Description of hood/housing | Black             |
| Type                        | High construction |

## Version

|                      |   |
|----------------------|---|
| Size                 | 16 B  |
| Version              | Top entry   |
| Cable entry          | 1x M25  |
| Locking type         | Double locking lever                              |
| Field of application | Standard hoods/housings for industrial connectors |

## Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65   |
|  | IP66   |
|  | IP67   |
| Type rating acc. to UL 50 / UL 50E     | 4  |
|  | 4X   |
|  | 12   |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                            |
|--------------------------------------|----------------------------|
| Material (hood/housing)              | Aluminium die-cast         |
| Surface (hood/housing)               | Powder-coated              |
| Colour (hood/housing)                | RAL 9005 (jet black)       |
| RoHS                                 | compliant                  |
| ELV status                           | compliant                  |
| China RoHS                           | e                          |
| REACH Annex XVII substances          | Not contained              |
| REACH ANNEX XIV substances           | Not contained              |
| REACH SVHC substances                | Not contained              |
| California Proposition 65 substances | Yes                        |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)       |
| Requirement set with Hazard Levels   | R1 (HL 1-3)<br>R7 (HL 1-3) |

## Specifications and approvals

|           |              |
|-----------|--------------|
| Approvals | CE<br>DNV GL |
|-----------|--------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 222.2 g                                  |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140127982                            |
| ETIM                           | EC000437                                 |
| eCI@ss                         | 27440202 Shell for industrial connectors |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19307160426](#)