



Pushing Performance  
Since 1945

# Han 10B-SCP-HTE-HC-f. DL-M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 910 0427
Specification	Han 10B-SCP-HTE-HC-f. DL-M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19309100427">https://b2b.harting.com/19309100427</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han® B
Type of hood/housing	Hood
Description of hood/housing	Corrosion resistant
Type	High construction

## Version

Size	10 B
Version	Top entry
Cable entry	1x M32
Locking type	Double locking lever
Field of application	Standard hoods/housings for industrial connectors

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP66 IP67
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance  
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	1
Net weight	153 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140164451
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19309100427](#)