

## Han B Top Entry LC M20 Exi\_For Double Le



Image is for illustration purposes only. Please refer to product description.

Part number	19 36 010 1420
Specification	Han B Top Entry LC M20 Exi_For Double Le
HARTING eCatalogue	<a href="https://b2b.harting.com/19360101420">https://b2b.harting.com/19360101420</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> Ex
Type of hood/housing	Hood

### Version

Size	10 B
Version	Top entry
Cable entry	1x M20
Locking type	Double locking lever
Field of application	Connectors for explosion hazardous environments
Details	ATTENTION! Only to be used with Han <sup>®</sup> Ex inserts!

### Technical characteristics

Limiting temperature	-20 ... +40 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 With cable gland

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
 Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

## Commercial data

Packaging size	1
Net weight	310 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140181557
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19360101420](#)