

Han 24Ex UL-HTE-M25



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 36 524 1421 |
| Specification | Han 24Ex UL-HTE-M25 |
| HARTING eCatalogue | https://b2b.harting.com/19365241421 |

Identification

| | |
|--------------------------|---------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] Ex |
| Type of hood/housing | Hood |

Version

| | |
|----------------------|--|
| Size | 24 B |
| Version | Top entry |
| Cable entry | 1x M25 |
| Locking type | Double locking lever |
| Field of application | Connectors for explosion hazardous environments |
| Details | for US purposes only |
| Details | ATTENTION! Only to be used with Han [®] Ex inserts! |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -20 ... +40 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65 With cable gland |

Material properties

| | |
|-------------------------|---------------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 5015 (sky blue) |
| RoHS | compliant |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---------------|
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead |
| | Nickel |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 527 g |
| Country of origin | China |
| European customs tariff number | 85389099 |
| GTIN | 5713140181809 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19365241421](#)