

## Han 6HP Direct/B-HSE-M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 39 606 0547
Specification	Han 6HP Direct/B-HSE-M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19396060547">https://b2b.harting.com/19396060547</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> HP Direct B
Type of hood/housing	Hood

### Version

Size	6 B
Version	Side entry
Cable entry	1x M32
Locking type	Screw locking

### Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP66 IP68 IP69 / IPX9K acc. to ISO 20653

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Stainless steel



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE

## Commercial data

Packaging size	1
Net weight	250 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140182332
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19396060547](#)