



Pushing Performance  
Since 1945

# Han 24HPR-Compact-HSE-LC-SCL-M40



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 40 524 1513  |
| Specification      | Han 24HPR-Compact-HSE-LC-SCL-M40  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19405241513">https://b2b.harting.com/19405241513</a> |

## Identification

|                          |                  |
|--------------------------|------------------|
| Category                 | Hoods/Housings   |
| Series of hoods/housings | Han® HPR Compact |
| Type of hood/housing     | Hood             |
| Type                     | Low construction |

## Version

|                      |   |
|----------------------|---|
| Size                 | 24 B  |
| Version              | Side entry                                    |
| Cable entry          | 1x M40  |
| Locking type         | Screw locking                                 |
| Field of application | Hoods/housings for harsh outdoor environments |

## Technical characteristics

|  |  |
|--|--|
| Tightening torque (screw locking)      | 4 Nm   |
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65   |
|  | IP68   |
|  | IP6K9K acc. to ISO 20653                       |
| Type rating acc. to UL 50 / UL 50E     | 4  |
|  | 4X   |
|  | 12   |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |   |
|--------------------------------------|---|
| Material (hood/housing)              | Aluminium die-cast<br>Corrosion resistant |
| Surface (hood/housing)               | Powder-coated                             |
| Colour (hood/housing)                | RAL 9005 (jet black)                      |
| Material (locking)                   | Stainless steel                           |
| RoHS                                 | compliant                                 |
| ELV status                           | compliant                                 |
| China RoHS                           | e   |
| REACH Annex XVII substances          | Not contained                             |
| REACH ANNEX XIV substances           | Not contained                             |
| REACH SVHC substances                | Not contained                             |
| California Proposition 65 substances | Not contained                             |

## Specifications and approvals

|           |  |
|-----------|--|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL   |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 445 g                                    |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140174450                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19405241513](#)