



Pushing Performance
Since 1945

Han-Eco Mod.6 TC70-MI-CRT



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 006 3002
Specification	Han-Eco Mod.6 TC70-MI-CRT
HARTING eCatalogue	https://b2b.harting.com/19410063002

Identification

Category	Inserts
Series	Han-Eco®

Version

Termination method	Crimp termination
Gender	Male
Size	10 B
Number of contacts	6
PE contact	Yes
Details	Please order crimp contacts separately.
	Working Contacts: TC 70 Contacts
	PE Contact: Han-Eco Mod.-SMC-MC/FC-CRT-PE
	Including contact bridge (three contacts)
	Coding version 1

Technical characteristics

Conductor cross-section	4 ... 25 mm²
Rated current	70 A
Rated voltage	1,000 V
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥500
---------------	------

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	1
Net weight	27.3 g
Country of origin	USA
European customs tariff number	85366990
GTIN	5713140830387
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19410063002](#)