



Pushing Performance
Since 1945

Han-Eco 24B-Cover-w. SL-w. cord-HTE/HSE

	Part number	19 43 024 5442
	Specification	Han-Eco 24B-Cover-w. SL-w. cord-HTE/HSE

Identification

Category	Accessories
Series of hoods/housings	Han-Eco® B
Type of accessory	Protection cover
Description of the accessory	for hoods

Version

Size	24 B
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94
(locking levers)

V-0

RoHS

compliant

ELV status

compliant

China RoHS

e

REACH Annex XVII substances

Not contained

REACH ANNEX XIV substances

Not contained

REACH SVHC substances

Not contained

Fire protection on railway vehicles

EN 45545-2 (2020-08)

Requirement set with Hazard Levels

R22 (HL 1-3)

R23 (HL 1-3)

Specifications and approvals

Specifications

IEC 61984

EN 45545-2 Fire protection on railway vehicles

Commercial data

Packaging size

1

Net weight

85 g

Country of origin

Germany

European customs tariff number

85389099

ETIM

EC002314

eCI@ss

27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19430245442](#)