



Pushing Performance
Since 1945

Han INOX 3A R/A Bulkhead Mounted Housing



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 44 003 0801 |
| Specification | Han INOX 3A R/A Bulkhead Mounted Housing |
| HARTING eCatalogue | https://b2b.harting.com/19440030801 |

Identification

| | |
|-----------------------------|--------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-INOX® |
| Type of hood/housing | Bulkhead mounted housing |
| Description of hood/housing | Angled |

Version

| | |
|----------------------|---------------------------------------|
| Size | 3 A |
| Locking type | Single locking lever |
| Field of application | Hoods/housings for harsh environments |
| Pack contents | With seal screw |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP44 IP65 With seal screw IP67 With seal screw |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-------------------------|-----------------|
| Material (hood/housing) | Stainless steel |
| Surface (hood/housing) | Uncoated |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|-----------------------|
| Colour (hood/housing) | Unpainted |
| Material (seal) | FPM |
| Material (locking) | Stainless steel |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel Naphthalene |

Specifications and approvals

| | |
|-----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 20 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140131941 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19440030801](#)