

Han INOX 3A SE Hood M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 003 1640
Specification	Han INOX 3A SE Hood M20
HARTING eCatalogue	https://b2b.harting.com/19440031640

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Hood

Version

Size	3 A
Version	Side entry
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Hoods/housings for harsh environments
Pack contents	With seal screw

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44
	IP65 With seal screw
	IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Stainless steel
-------------------------	-----------------



Pushing Performance
Since 1945

Material properties

Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

Commercial data

Packaging size	1
Net weight	77 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140131996
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19440031640](#)