

# Han-INOX 3A-HCC-M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 003 1750
Specification	Han-INOX 3A-HCC-M20
HARTING eCatalogue	<a href="https://b2b.harting.com/19440031750">https://b2b.harting.com/19440031750</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Cable to cable housing

## Version

Size	3 A
Version	Top entry
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Hoods/housings for harsh environments
Pack contents	With seal screw

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44
	IP65 With seal screw
	IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

Material (hood/housing)	Stainless steel
-------------------------	-----------------



**Pushing Performance**  
Since 1945

## Material properties

Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

## Commercial data

Packaging size	1
Net weight	84 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140163652
ETIM	EC000437
eCI@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19440031750](#)