



Pushing Performance
Since 1945

Acces. Special Cable Clamp EMC M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 000 5092
Specification	Acces. Special Cable Clamp EMC M25
HARTING eCatalogue	https://b2b.harting.com/19620005092

Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Wrench size	28
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	M25
Clamping range	9 ... 13 mm
Shielding diameter	4.8 ... 8 mm
Width across corners	31.2 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

Commercial data

Packaging size	10
Net weight	45 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140132221
ETIM	EC000441
eCl@ss	27140803 Cable gland EMC (electrical installation)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19620005092](#)