

# Han 40EMC-HTE-M40



Part number	19 62 040 0443
Specification	Han 40EMC-HTE-M40
HARTING eCatalogue	https://b2b.harting.com/19620400443

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> EMC
Type of hood/housing	Hood

#### Version

Size	16 B
Version	Top entry
Cable entry	1x M40
Locking type	Screw locking
Field of application	Hoods/Housings for higher EMC requirements

#### Technical characteristics

Limiting temperature	-40 +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant



## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

#### Commercial data

Packaging size	1
Net weight	272 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140171510
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# HARTING:

19620400443