



Pushing Performance  
Since 1945

# Han 10EMC/B-HTE-HC-for SL-M40-HMC



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 19 62 210 0448                                                                        |
| Specification      | Han 10EMC/B-HTE-HC-for SL-M40-HMC                                                     |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19622100448">https://b2b.harting.com/19622100448</a> |

## Identification

|                          |                   |
|--------------------------|-------------------|
| Category                 | Hoods/Housings    |
| Series of hoods/housings | Han® EMC/B        |
| Type of hood/housing     | Hood              |
| Type                     | High construction |

## Version

|                      |                                                                                                 |
|----------------------|-------------------------------------------------------------------------------------------------|
| Size                 | 10 B                                                                                            |
| Version              | Top entry                                                                                       |
| Cable entry          | 1x M40                                                                                          |
| Locking type         | Single locking lever                                                                            |
| Field of application | Hoods/Housings for higher EMC requirements<br>Special hoods and housings for high mating cycles |

## Technical characteristics

|                                         |                                                |
|-----------------------------------------|------------------------------------------------|
| Limiting temperature                    | -40 ... +125 °C                                |
| Note on the limiting temperature        | For use as a connector according to IEC 61984. |
| Mating cycles with other HMC components | ≥10,000                                        |
| Degree of protection acc. to IEC 60529  | IP65<br>IP66                                   |
| Type rating acc. to UL 50 / UL 50E      | 4<br>12                                        |

## Material properties

|                         |                    |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
|-------------------------|--------------------|



**Pushing Performance**  
Since 1945

## Material properties

|                        |           |
|------------------------|-----------|
| Surface (hood/housing) | Uncoated  |
| Colour (hood/housing)  | Unpainted |

## Specifications and approvals

|           |                                   |
|-----------|-----------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076             |
|           | CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE                                |
|           | DNV GL                            |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 150 g                                    |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140171817                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19622100448](#)