

# Han ID-Modul



Image is for illustration purposes only. Please refer to product description.

Part number	20 70 001 1001
Specification	Han ID-Modul
HARTING eCatalogue	<a href="https://b2b.harting.com/20700011001">https://b2b.harting.com/20700011001</a>

## Identification

Category	Modules
Series	Han-Modular®
Type of module	Han-Elisa® module
Size of the module	Single module

## Version

Gender	Male
Number of contacts	6

## Technical characteristics

Limiting temperature	0 ... +70 °C
----------------------	--------------

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance  
Since 1945

Material properties

REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	1
Net weight	29.5 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140134362
ETIM	EC000438
eCl@ss	27440218 Module for industrial connectors (data)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[20700011001](#)