



Pushing Performance
Since 1945

Har-speed M12 malecont. Crimp AWG 23-26



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9019
Specification	Har-speed M12 malecont. Crimp AWG 23-26
HARTING eCatalogue	https://b2b.harting.com/21011009019

Identification

Category	Contacts
Series	har-speed
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.13 ... 0.25 mm²
Conductor cross-section	AWG 26 ... AWG 23
Performance level	1

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	100
Net weight	0.06 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140136717
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21011009019](#)