

## Female contact crimp Pack d0,6 AWG28-24



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9023
Specification	Female contact crimp Pack d0,6 AWG28-24
HARTING eCatalogue	<a href="https://b2b.harting.com/21011009023">https://b2b.harting.com/21011009023</a>

### Identification

Category	Contacts
Series	har-speed
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.08 ... 0.22 mm <sup>2</sup>
Conductor cross-section	AWG 28 ... AWG 24
Performance level	1

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance  
Since 1945

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	100
Net weight	0.1 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140229549
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21011009023](#)