

# M12 female contact Pack D0.8mm AWG 26-22



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9025
Specification	M12 female contact Pack D0.8mm AWG 26-22
HARTING eCatalogue	<a href="https://b2b.harting.com/21011009025">https://b2b.harting.com/21011009025</a>

## Identification

Category	Contacts
Series	Circular connectors M12
Type of contact	Crimp contact

## Version

Gender	Female
Manufacturing process	Turned contacts

## Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 22
Rated current	≤2 A
Performance level	1

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

## Commercial data

Packaging size	100
Net weight	0.1 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140229280
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21011009025](#)