

M12 Power female crimp contact PE0,75mm²



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9965
Specification	M12 Power female crimp contact PE0,75mm ²
HARTING eCatalogue	https://b2b.harting.com/21011009965

Identification

Category	Contacts
Series	Circular connectors M12
Identification	Power
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.75 mm ²
Conductor cross-section	AWG 19
Performance level	1

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Commercial data

Packaging size	50
Net weight	0.56 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140229426
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21011009965](#)