

Circular Con. M12 crimp male A-code 5pol



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 812 1505
Specification	Circular Con. M12 crimp male A-code 5pol
HARTING eCatalogue	https://b2b.harting.com/21038121505

Identification

Category	Connectors
Series	Circular connectors M12
Element	Cable connector
Specification	Straight

Version

Termination method	Crimp termination
Gender	Male
Shielding	Shielded
Number of contacts	5
Coding	A-coding
Locking type	Screw locking
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 0.75 mm ²
Conductor cross-section	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	48 V AC 60 V DC
Rated impulse voltage	1.5 kV
Pollution degree	3



Pushing Performance
Since 1945

Technical characteristics

Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	17
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.5 ... 8.8 mm
Isolation group	I ($600 \leq \text{CTI}$)

Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	1
Net weight	44.8 g
Country of origin	Germany
European customs tariff number	85366990



Pushing Performance
Since 1945

Commercial data

GTIN	5713140139510
ETIM	EC002635
eCl@ss	27440116 Circular connector (for field assembly)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21038121505](#)